

# Hytrex\*

melt blown depth filter for high purity water systems



## features and benefits

- Well-suited for high purity applications with fast rinse-ups due to superior construction
- Automated packaging and manufacturing processes ensure a clean, reliable product every time
- Meets stringent requirements for most critical processes
- Pure polypropylene construction
- Wide chemical compatibility
- Combines efficiency, long, life, and purity

## applications

- High purity chemicals
- Potable water filtration
- Food and beverage
- Reverse osmosis prefiltration
- Electronics

## specifications

**Table 1: Specifications and performance information**

<b>Ratings</b>	1, 3, 5, 10, 20, 30, 50, 75, 100 microns (nominal)	
<b>Inner Diameter (nominal)</b>	1 in (2.5 cm)	
<b>Outer Diameter</b>	2.5 in (6.4 cm)	
<b>Lengths</b>	4 7/8 in (12.4 cm)	29 1/4 in (74.3 cm)
	9 3/4 in (24.8 cm)	30 in (76.2 cm)
	10 in (25.4 cm)	40 in (101.6 cm)
	19 1/2 in (49.5 cm)	50 in (152.4 cm)
	20 in (50.8 cm)	

*Longer lengths up to 70 in may be available upon request*

### Materials of Construction

Filter Media	Polypropylene
Adapters	Polypropylene
Elastomer	Buna, EPDM, Silicone, Viton <sup>1</sup> , Santoprene <sup>2</sup> (flat gasket only)

### Performance Conditions

Maximum pressure drop:	35 psid (2.4 bar) @ 77°F (25°C)
Recommended change-out pressure drop:	20 psid (1.4 bar) @ 77°F (25°C)

## efficiency information


**Table 2: Removal efficiency based on a modified ASTM 795 test procedure**

Micron Rating	Removal rating (µm) at various efficiencies		
	90.0%	99.0%	99.9%
1 µm			
3 µm	<i>Efficiency of nominal filters varies by application. See note for information on nominal filter efficiency<sup>3</sup></i>		
5 µm			
10 µm			
20+ µm			

Find a contact near you by visiting [www.suezwatertechnologies.com](http://www.suezwatertechnologies.com) and clicking on "Contact Us."

\*Trademark of SUEZ; may be registered in one or more countries.

©2019 SUEZ. All rights reserved.



**Graph 1: Hytrex clean water flow rate based on a 10 in length filter**

### quality

Hytrex filters are manufactured under a quality management system that has been certified to meet ISO 9001 standards. Each filter is assigned a lot code to ensure traceability of the data and materials used in the manufacturing process.

### certifications


- U.S. FDA 21CFR 177.1520 food contact requirements
- Article 3 of the EU Framework Regulation No. 1935/2004/EC safety requirements
- EU Plastics Regulation No. 10/2011 (may be used as intended in all compliant EU Member states)
- USP class VI-121°C Plastics criteria
- NSF 42 and 61 criteria
- ISO 9001 criteria

SUEZ filter cartridges are designed and manufactured for resistance to a wide range of chemical solutions. Conditions will vary with each application and users should carefully verify chemical compatibility. Please contact your SUEZ representative for more information.

### ordering information

Replace the numbers with your desired values from each column. Columns 3, 4, and 5 are optional depending on the desired configuration. Use "-B" if you would like bulk packaging.

**Example:** GX 05-29 1/4-YYP



**Table 3: Ordering information**

	1	2	3	4	5
Type	Micron Rating (nominal)	Cartridge Length	End #1 Adapter	End #2 Adapter	Elastomer Material
GX	01 = 1 µm	4 7/8 in (12.4 cm)	E = 222 O-Ring	H = Fin	B = Buna E = EPDM P = Santoprene <sup>2</sup> (flat gasket only) S = Silicone V = Viton <sup>1</sup>
	03 = 3 µm	9 3/4 in (24.8 cm)	F = 226 O-Ring	K = Self Seal Spring	
	05 = 5 µm	10 in (25.4 cm)	L = Extended Core	S = Solid End	
	10 = 10 µm	19 1/2 in (49.5 cm)	X = Standard Plain End (no gasket)	X = Standard Plain End (no gasket)	
	20 = 20 µm	20 in (50.8 cm)	Y = Flat Gasket	Y = Flat Gasket	
	30 = 30 µm	29 1/4 in (74.3 cm)			
	50 = 50 µm	30 in (76.2 cm)			
	75 = 75 µm	40 in (101.6 cm)			
	100 = 100 µm	50 in (152.4 cm)			
		<i>Longer lengths up to 70 in may be available upon request</i>			

<sup>1</sup>Viton is a registered mark of DuPont

<sup>2</sup>Santoprene is licensed to Advanced Elastomer Systems, L.P.

<sup>3</sup>Absolute-rated filters have been designed and tested to reject at least 99% of particles of the listed micron size. Nominal-rated filters have a wider distribution of pore sizes and therefore a wider distribution of rejected particle sizes. The nominal rating is primarily used to compare efficiencies across a filter family and between filter manufacturers. Efficiency is dependent on particle shape, size, composition, application, and testing protocol.

